

Vacuum Atmosphere Pit Furnace

GWL-ZQJ



GWL Series 1200°C-1800°C High Temperature Vacuum Atmosphere Pit Furnace

The equipment designed for pyrolysis, melting, analysis and production ceramics, metallurgy, electronics, machinery, chemical, glass, refractories, for develop new material, special materials, construction materials, the equipment is suitable for institutions of higher learning and laboratory of scientific research institute and industrial and mining enterprises.

The control panel equipped with the intelligent adjustment device, power control switch, main working/stop button, voltmeter, ammeter, Computer interface, Observe port / Air inlet port, for convenience to observe the furnace working status, the product using reliable integrated circuit, excellent working environment, anti-interference, the highest temperature of furnace shell temperature is less than 45 can greatly improve the working environment. micro computer program control, programmable setting temperature rise curve, Fully automatic temperature rise / cooling, Temperature control parameters and programs can be modified during operation, which is flexible, convenient and simple in operation.

Temperature Control Accuracy : $\pm 1^{\circ}\text{C}$, Temperature Constant Accuracy: $\pm 1^{\circ}\text{C}$. Fast Temperature rise rate, Maximum heating rate $\leq 30^{\circ}\text{C}/\text{min}$. Furnace hearth materials made up by vacuum forming high purity alumina light materials (Will be changing due to the temperature required), High temperature for use, Less heat storage amount, Tolerance the extremely heating and cold, no crack, No dregs, Excellent thermal insulation performance (the energy saving effect is over 60% of the traditional furnace). Reasonable structure, Double layer furnace cover, Air cooling, Greatly shortening the experimental period.



Model	GWL-ZQJ				
Working Temperature	1200°C	1400°C	1600°C	1700°C	1800°C
Maximum Temperature	1250°C	1450°C	1650°C	1750°C	1820°C
Heating Element	Silicon Carbide Rod		Silicon molybdenum rod		
Diameter Of Furnace Hearth	200MM 300MM 500MM 600MM				
Height of furnace hearth	300MM 500MM 800MM 1000MM				
Vacuum Degree	-0.1MPa				
Temperature Rise Rate	Temperature Rise Rate Can Be Modify (30°C/min 1°C/h) , Company Suggest 10-20°C/min.				
Pressure Protection	The system is specially made to prevent the danger of closure of the exhaust port, the blockage of the exhaust port and the excessive pressure of the furnace tube. The signal is obtained by the electric contact pressure meter or pressure sensor then the drive control module will close the electromagnetic inlet valve and starts the electromagnetic exhaust valve and the alarm. to ensure the furnace can be used properly and safely.				
Rated Voltage	380V				
Temperature Uniformity	±1°C				
Temperature Control Accuracy	±1°C				
Furnace Inner Tank Materials	Sealed with the stainless steel 310S Material (Vary according furnace temperature) Can be removable under high temperature environment.				
Furnace Lining Materials	Alumina Polymer Light Material				
Vacuum Pump	Double stage direct rotary vane vacuum pump				
Standard Accessories	Heating Elements, Specification Certificate, Heat Insulation Brick, Crucible Pliers, High Temperature Gloves.				

Characteristic:**Operational Simplicity, Less land occupation, Top open.**

1. Temperature accuracy: ±1°C ; Constant temperature: ±1°C (Base on Heating zone size) .
2. Simplicity for operation, programmable, PID automatic modify, automatic temperature rise, automatic temperature retaining, automatic cooling, unattended operation
3. Cooling structure: Air + Water Cooling.
4. Furnace surface temperature approach the indoor temperature.
5. double layer loop protection. (over temperature protection, over pressure protection, over current protection, thermocouple protection, Power supply protection and so on)
6. Importing refractory, excellent temperature retaining effect, high temperature resistance, Tolerance the extreme heat and cold
7. More gas options (Oxygen、Nitrogen、Argon、hydrogen and so on)

Furnace Hearth And Atmosphere Can Be Customized, More Details Please Contact Us