



## Lift Tube Furnace (GWL-GAS)



### GWL Series 1200°C-1800°C Lift Tube Furnace

The equipment designed for pyrolysis, melting, analysis and production ceramics, metallurgy, electronics, machinery, chemical, glass, refractories, for develop new material, special materials, construction materials, the equipment is suitable for institutions of higher learning and laboratory of scientific research institute and industrial and mining enterprises.

The control panel equipped with the intelligent adjustment device, power control switch, main working/stop button, voltmeter, ammeter, Computer interface, Observe port / Air inlet port, for convenience to observe the furnace working status, the product using reliable integrated circuit, excellent working environment, anti-interference, the highest temperature of furnace shell temperature is less than 45 can greatly improve the working environment, micro computer program control, programmable setting temperature rise curve, Fully automatic temperature rise / cooling, Temperature control parameters and programs can be modified during operation, which is flexible, convenient and simple in operation.

Temperature Control Accuracy:  $\pm 1^{\circ}\text{C}$ , Temperature Constant Accuracy:  $\pm 1^{\circ}\text{C}$ . Fast Temperature rise rate, Maximum heating rate  $\leq 30^{\circ}\text{C}/\text{min}$ . Furnace hearth materials made up by vacuum forming high purity alumina light materials (Will be changing due to the temperature required), High temperature for use, Less heat storage amount, Tolerance the extremely heating and cold, no crack, No dregs, Excellent thermal insulation performance (the energy saving effect is over 60% of the traditional furnace). Reasonable structure, Double layer furnace cover, Air cooling, Greatly shortening the experimental period.



Model	GWL-GAS				
Working Temperature	1200°C	1400°C	1600°C	1700°C	1800°C
Maximum Temperature	1250°C	1450°C	1650°C	1750°C	1820°C
Heating Element	Silicon Carbide Rod		Silicon molybdenum rod		
Diameter Of Tube	30mm  50mm  60mm  80mm  90mm  100mm  110mm  150mm (Can be Customized)				
Length Of Heating Zone	150mm  250mm  300mm  400mm  500mm  600mm   700mm  1000mm  1200mm (Can be Customized)				
Tube Materials	Below 1400°C: Stainless Steel Tube /quartz glass tube / corundum tube Above 1400°C: Corundum tube				
Lift Method	Electric Machinery Lift (Lift Speed adjustable)				
Temperature Rise Rate	Temperature Rise Rate Can Be Modify (30°C/min   1°C/h) Company Suggest 10-20°C/min.				
Vacuum Degree	-0.1Mpa (Can Customize As 1Pa, -1Pa, -0.01Pa and so on)				
Rated Voltage	380V				
Temperature Uniformity	±1°C				
Temperature Control Accuracy	±1°C				
Standard Accessories	Heating Elements, Specification Certificate, Heat Insulation Brick, Crucible Pliers, High Temperature Gloves. Special crucible for tube furnace, seal rings				
<b>Characteristic:</b>					
<ol style="list-style-type: none"> <li>1. Temperature accuracy: ±1°C ; Constant temperature: ±1°C(Base on Heating zone size ) 。</li> <li>2. Simplicity for operation, programmable , PID automatic modify, automatic temperature rise, automatic temperature retaining, automatic cooling, unattended operation</li> <li>3. Cooling structure: Double layer furnace shell, air cooling and water cooling</li> <li>4. Furnace surface temperature approach the indoor temperature.</li> <li>5. double layer loop protection. (over temperature protection, over pressure protection, over current protection, thermocouple protection, Power supply protection and so on)</li> <li>6. Importing refractory, excellent temperature retaining effect, high temperature resistance, Tolerance the extreme heat and cold</li> <li>7. More gas options (Oxygen、Nitrogen、Argon、hydrogen and so on)</li> <li>8. Furnace hearth materials: 1200°C: High Purity Alumina Fiber Board; 1400°C: High purity alumina (Contain zirconium) fiberboard; 1600°C: Import High Purity Alumina Fiber Board; 1700°C-1800°C: High Purity alumina polymer fiber board.</li> </ol>					
Tube Dimension Can Be Customize , More Details Please Contact Us.					